


Split Bottom Plates Stainless Steel, CBPS



A split bottom plate offers a flexible cabling solution and eliminates the need for individual cable glands. The protection degree is maintained by using a separate gasket.

FEATURES

Description: Fitted in place of the standard one piece bottom plate, allows direct cable entry. To achieve perfect sealing around the cables use the gasket kit BG01.

Material: AISI 304 / AISI 316L pre-grained stainless steel.

Bottom plates: 1.5 mm.

Finish: 400 pre-grained stainless steel.

Pack quantity: 1 kit of two part bottom plate.

Finish: Brushed

Thickness: 1.5mm

SPECIFICATIONS

Catalog Number	E-Number	Height	Width	Depth	Enclosure Material	Material
CBPS0640	2502424	25mm	600mm	400mm	Stainless Steel	Stainless Steel 304
CBPS0640-316	2502425	25mm	600mm	400mm	Stainless Steel	Stainless Steel 316
CBPS0650	2502426	25mm	600mm	500mm	Stainless Steel	Stainless Steel 304
CBPS0650-316	2502427	25mm	600mm	500mm	Stainless Steel	Stainless Steel 316
CBPS0660	2502428	25mm	600mm	600mm	Stainless Steel	Stainless Steel 304
CBPS0660-316	2502429	25mm	600mm	600mm	Stainless Steel	Stainless Steel 316
CBPS0840	2502430	25mm	800mm	400mm	Stainless Steel	Stainless Steel 304
CBPS0840-316	2502431	25mm	800mm	400mm	Stainless Steel	Stainless Steel 316
CBPS0850	2502432	25mm	800mm	500mm	Stainless Steel	Stainless Steel 304
CBPS0850-316	2502433	25mm	800mm	500mm	Stainless Steel	Stainless Steel 316
CBPS0860	2502434	25mm	800mm	600mm	Stainless Steel	Stainless Steel 304
CBPS0860-316	2502435	25mm	800mm	600mm	Stainless Steel	Stainless Steel 316
CBPS1040	2502436	25mm	1000mm	400mm	Stainless Steel	Stainless Steel 304
CBPS1040-316	2502437	25mm	1000mm	400mm	Stainless Steel	Stainless Steel 316

Catalog Number	E-Number	Height	Width	Depth	Enclosure Material	Material
CBPS1050	2502438	25mm	1000mm	500mm	Stainless Steel	Stainless Steel 304
CBPS1050-316	2502439	25mm	1000mm	500mm	Stainless Steel	Stainless Steel 316
CBPS1060	2502440	25mm	1000mm	600mm	Stainless Steel	Stainless Steel 304
CBPS1060-316	2502441	25mm	1000mm	600mm	Stainless Steel	Stainless Steel 316

ADDITIONAL PRODUCT DETAILS

For enclosures 1200 mm & 1600 mm wide use 2 x 600 mm & 2 x 800 mm wide bottom plates.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

