

# nVent CADDY Speed Link LD with Hook



## FEATURES

Complete system includes wire, locking device and pre-assembled hook end fitting

Hooks to a wide range of nVent CADDY fasteners

Fastens to the building structure or hanging services by looping around and hooking to wire rope

Easy to remove for applications requiring maintenance

Spring latch helps provide secure connection

Insert cable through hole and use bottom side of hook as an end stop

**Material:** Stainless Steel 304 (EN 1.4301)  
**Static Load Safety Factor:** 5:1  
**Wire Rope Diameter:** 1.5 mm



## SPECIFICATIONS

| Catalog Number | Article Number | Wire Rope Length | A       | B       | C      | Static Load |
|----------------|----------------|------------------|---------|---------|--------|-------------|
| SLD15L10S      | 195945         | 10m              | 58.4 mm | 22.9 mm | 6.4 mm | 195N        |
| SLD15L2S       | 195935         | 2m               | 58.4 mm | 22.9 mm | 6.4 mm | 195N        |
| SLD15L5S       | 195940         | 5m               | 58.4 mm | 22.9 mm | 6.4 mm | 195N        |

**Height (H):** 19 mm  
**Width (W):** 12.7 mm

## ADDITIONAL PRODUCT DETAILS

Wire and pre-assembled hook end fitting made of Stainless Steel 316 (1.4401).



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500

