

Threaded Stud

FEATURES

Pre-cut lengths of threaded rod




Material: Steel
Finish: Electrogalvanized
Quality Class: 4.6

SPECIFICATIONS

Catalog Number	Article Number	Rod Size (RS)	Length (L)
051M10025	400345	M10	25mm
051M10040	400346	M10	40mm
051M10060	400347	M10	60mm
051M10080	400349	M10	80mm
051M10090	593505	M10	90mm
051M10100	400351	M10	100mm
051M10150	593516	M10	150mm
051M8025	400336	M8	25mm
051M8040	400337	M8	40mm
051M8060	400338	M8	60mm
051M8070	593465	M8	70mm
051M8080	400340	M8	80mm

Catalog Number	Article Number	Rod Size (RS)	Length (L)
051M8100	400342	M8	100mm
051M8120	593476	M8	120mm
051M8150	593477	M8	150mm

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

