

SCH1 Single Piece Strut Clamp for Conduit



FEATURES


- One-piece conduit clamp
- No screws or bolts to drop
- Requires only a screwdriver or nutdriver for installation
- Fits into open side of strut channel

Material: Steel
Finish: Electrogalvanized



SPECIFICATIONS

Catalog Number	Outer Diameter (OD)	Static Load
SCH12	14.5 - 23.4 mm	880N
SCH16	18.3 - 29.5 mm	880N
SCH20	25.4 - 38.4 mm	880N
SCH8	8.6 - 18 mm	880N



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

