

Hammer-On Flange Clip, Bottom Mount




FEATURES

Can be used to support boxes, fixtures or other applications from beam flanges

Assorted attachment points provided to reduce inventory

Requires only a hammer to install





SPECIFICATIONS

Table 1/2

Catalog Number	Article Number	Material	Finish	Flange Thickness (FT)	Rod Size (RS)	Static Load 1 (F1)
EM24S1	179720	Stainless Steel 301 (EN 1.4310)		3 - 8 mm	6	200N
EM58S1	179730	Stainless Steel 301 (EN 1.4310)		8 - 14 mm	6	200N
EM912S1	179740	Stainless Steel 301 (EN 1.4310)		14 - 20 mm	6	200N
M24		Spring Steel	nVent CADDY Armour	3 - 8 mm	6	440N
M58		Spring Steel	nVent CADDY Armour	8 - 14 mm	6	440N
M912		Spring Steel	nVent CADDY Armour	14 - 20 mm	6	440N

Table 2/2				
Catalog Number	Article Number	Static Load 2 (F2)	Static Load 3 (F3)	Certifications
EM24S1	179720	110N	200N	
EM58S1	179730	110N	200N	
EM912S1	179740	110N	200N	
M24		330N	110N	cUL, UL
M58		330N	110N	UL, cUL
M912		330N	110N	UL, cUL



APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



This document is system-generated.

