

# nVent CADDY Pyramid Tool-Free Cable Tray Support Kit



## FEATURES

Push-in pins install without the need for additional tools

Plastic pins and base will not corrode

Pins and mounting holes accommodate most perforated cable tray

Ready to use out of the box, saving installation time and labor

Additional pins can be purchased separately

Foam bottom offers low abrasion interface for better roof membrane protection

Provides superior load distribution, even with varying rooftop surfaces

Compatible with roof surfaces including single ply, bituminous, metal and spray foam


Multiple sizes and load ratings offer the ability to tailor the solution to the application

Easy to transport to the roof

**Material:** Polyethylene;Polypropylene;Nylon  
**Temperature:** -45 to 65 °C  
**Static Load Safety Factor:** 3:1

## SPECIFICATIONS

| Catalog Number | Article Number | Length (L) | Width (W) | Height (H) | Surface Area         | Unit Weight | Static Load |
|----------------|----------------|------------|-----------|------------|----------------------|-------------|-------------|
| PTF10P         | 360519         | 318mm      | 201 mm    | 102 mm     | 59355mm <sup>2</sup> | 0.5 kg      | 4450N       |
| PTF16P         | 360522         | 480mm      | 201 mm    | 102 mm     | 91613mm <sup>2</sup> | 1 kg        | 6670N       |
| PTF6P          | 360518         | 196mm      | 150 mm    | 102 mm     | 26452mm <sup>2</sup> | 0.3 kg      | 1330N       |



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500

