

External Horizontal Wall Bracket, Steel, Electrogalv., E4 Channel, A, C Strut

CATALOG NUMBER

APYE4STRUTEG

FEATURES

Side mount saddle support for C-Profiles and strut

Complete with fixings



PRODUCT ATTRIBUTES

Article Number: 584751

Material: Steel

Finish: Electrogalvanized

Channel Type: E4

Strut Type: A (41 x 41 mm);C (21 x 41 mm)

Height (H): 50 mm

Width (W): 144 mm


Thickness (T): 5 mm

A: 43 mm

B: 12 mm

C: 19 mm

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

