



		$\cdot$ = can be combined, $+$ = combination not recommended			
 100% L		-	+	+	not recommended for roof
	 50% L + L	+	not recommended for flat roofs (see compatibility)	not recommended for steep roofs (see compatibility)	+
	 100% L + L	+	+	+	+
100% L + L		not recommended for light	not recommended for flat roofs	-	-
	 50% L + L	+	+	-	-
	 100% L + L	+	+	-	-
100% L + L + L	 100% L + L	+	+	+	+
100% L + L + L	 50% L + L + L	+	+	+	+
100% L + L + L	 100% L + L + L	+	+	+	+

34566-242

FEATURES

Aluminum extrusion, anodized finish, conductive contact surface, with HP markings



Gross Weight: 0.132kg

Without M4 thread to front, without printing and without notch for 19" bracket.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

