

101 Loop Hanger for Copper Tube



FEATURES


Recommended for the suspension of stationary non-insulated copper tube lines

Conforms with Federal Specification WW-H-171 (Type 10), Manufacturers Standardization Society (MSS) SP-58 (Type 10)

Material: Steel
Finish: Copper Electroplated;Electrogalvanized

SPECIFICATIONS

Catalog Number	Pipe Size	Outer Diameter (OD)	Rod Size (RS)	A	B	C	Static Load (F)
1010050CP	1/2"	5/8"	3/8"	3 3/16"	1 5/8"	1 9/16"	180lbf
1010075CP	3/4"	7/8"	3/8"	3 1/8"	1 3/8"	1 3/16"	180lbf
1010100CP	1"	1 1/8"	3/8"	3 1/8"	1 5/16"	1"	180lbf
1010125CP	1 1/4" Min	1 3/8"	3/8"	3 3/16"	1 1/4"	13/16"	180lbf
1010150CP	1 1/2"	1 5/8"	3/8"	3 5/8"	1 9/16"	15/16"	180lbf
1010200CP	2" Min	2 1/8"	3/8"	3 13/16"	1 7/16"	5/8"	180lbf
1010250CP	2 1/2"	2 5/8"	3/8"	4 7/16"	1 11/16"	9/16"	200lbf
1010300CP	3"	3 1/8"	1/2"	5 11/16"	2 1/2"	1 5/16"	250lbf
1010400CP	4"	4 1/8"	1/2"	7 1/8"	3 7/16"	1 3/4"	360lbf



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

