

107 Wraparound Strap for CPVC Pipe



FEATURES

- Includes flared edges to protect piping
- Rated for use with CPVC fire sprinkler pipe
- Includes mounting screw

Material: Steel
Finish: Pregalvanized



SPECIFICATIONS

Catalog Number	Pipe Size	Outer Diameter (OD)	Hole Size (HS)	A	B	C	Hanger Spacing
1070075EG	3/4"	1.05"	7/32"	1 1/4"	2 3/8"	1 3/16"	5.5' Max
1070100EG	1"	1.31"	7/32"	1 7/16"	2 11/16"	1 3/16"	6' Max
1070125EG	1 1/4" Min	1.66"	7/32"	1 5/8"	3 1/16"	1 3/16"	6.5' Max
1070150EG	1 1/2"	1.9"	7/32"	1 3/4"	3 5/16"	1 3/16"	7' Max
1070200EG	2" Min	2 3/8"	7/32"	1 7/8"	3 11/16"	1 3/16"	8' Max



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

