

310 Universal Beam Clamp, Thick Flange



FEATURES

Universal beam clamp for thick beams

Conforms with Federal Specification WW-H-171 (Type 23), Manufacturers Standardization Society (MSS) SP-58 (Type 19 and 23)

Material: Cast Iron



SPECIFICATIONS

Table 1/2

Catalog Number	Finish	Rod Size (RS)	Rod Size (RS)	Flange Thickness (FT)	A	Torque (TQ)
3100037EG	Electrogalvanized	3/8"	3/8"	1 1/4" Max	1"	5 ft·lbf
3100037PL	Plain	3/8"	3/8"	1 1/4" Max	1"	5 ft·lbf
3100050EG	Electrogalvanized	1/2"	1/2"	1 1/4" Max	1"	11 ft·lbf
3100050PL	Plain	1/2"	1/2"	1 1/4" Max	1"	11 ft·lbf


Table 2/2

Catalog Number	Static Load 1 (F1)	Static Load 2 (F2)
3100037EG	500lb	250lb
3100037PL	500lb	250lb
3100050EG	950lb	760lb
3100050PL	950lb	760lb

ADDITIONAL PRODUCT DETAILS

Setscrew must be tightened and torqued onto the sloped side of the I-beam.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

