

401 Clevis Hanger



FEATURES

Recommended for the suspension of stationary non-insulated pipe lines

Flared edges help prevent sharp surfaces from coming into contact with the pipe (1/2" to 2" pipe sizes)

Clevis bottom pivots to allow pipe to be fed from either direction

Conforms with Federal Specification WW-H-171 (Type 1), Manufacturers Standardization Society (MSS) SP-58 (Type 1)

Material: Steel



SPECIFICATIONS

Table 1/2

Catalog Number	Finish	Pipe Size	Outer Diameter (OD)	Rod Size (RS)	A	B
4010050EG	Electrogalvanized, Pregalvanized	1/2"	0.84"	3/8"	2 5/16"	1 1/8"
4010075EG	Electrogalvanized, Pregalvanized	3/4"	1.05"	3/8"	2 1/2"	1 1/4"
4010100EG	Electrogalvanized, Pregalvanized	1"	1.31"	3/8"	2 13/16"	1 3/8"
4010125EG	Electrogalvanized, Pregalvanized	1 1/4" Min	1.66"	3/8"	3 1/8"	1 9/16"
4010150EG	Electrogalvanized, Pregalvanized	1 1/2"	1.9"	3/8"	3 11/16"	2 1/16"
4010200EG	Electrogalvanized, Pregalvanized	2" Min	2 3/8"	3/8"	4 5/16"	2 1/2"
4010250EG	Electrogalvanized, Pregalvanized	2 1/2"	2 7/8"	1/2"	5 5/16"	3 1/16"
4010250HD	Hot-Dip Galvanized	2 1/2"	2 7/8"	1/2"	5 1/4"	2 13/16"
4010300EG	Electrogalvanized, Pregalvanized	3"	3 1/2"	1/2"	6 1/16"	3 1/2"
4010300HD	Hot-Dip Galvanized	3"	3 1/2"	1/2"	6"	3 1/4"
4010350EG	Electrogalvanized, Pregalvanized	3 1/2"	4"	1/2"	6 13/16"	4"

Catalog Number	Finish	Pipe Size	Outer Diameter (OD)	Rod Size (RS)	A	B
4010400EG	Electrogalvanized, Pregalvanized	4"	4 1/2"	5/8"	7 7/16"	4 3/8"
4010400HD	Hot-Dip Galvanized	4"	4 1/2"	5/8"	7 3/4"	4 1/4"
4010500EG	Electrogalvanized, Pregalvanized	5"	5 9/16"	5/8"	9 1/16"	5 1/8"
4010600EG	Electrogalvanized, Pregalvanized	6"	6 5/8"	3/4"	10 9/16"	6"
4010800EG	Electrogalvanized, Pregalvanized	8"	8 5/8"	3/4"	14"	8"
4011000EG	Electrogalvanized, Pregalvanized	10"	10 3/4"	7/8"	16 1/2"	9"
4011200EG	Electrogalvanized, Pregalvanized	12"	12 3/4"	7/8"	18 5/8"	10 3/16"
4011400EG	Electrogalvanized, Pregalvanized	14"	14"	1"	21 3/4"	12 1/8"
4011600EG	Electrogalvanized, Pregalvanized	16"	16"	1"	24"	13 1/2"

Table 2/2

Catalog Number	Finish	Pipe Size	Outer Diameter (OD)	Rod Size (RS)	A	B
4011800EG	Electrogalvanized, Pregalvanized	18"	18"	1 1/8"	26 3/4"	15"
4012000EG	Electrogalvanized, Pregalvanized	20"	20"	1 1/4"	30"	17"


Table 1/2

Catalog Number	C	Static Load (F)	Certifications
4010050EG	3/8"	600lbf	cUL, ITB, UL
4010075EG	3/8"	600lbf	cUL, UL, ITB
4010100EG	3/8"	600lbf	cUL, UL, ITB
4010125EG	3/8"	600lbf	ITB, cUL, UL
4010150EG	11/16"	600lbf	ITB, cUL, UL
4010200EG	7/8"	600lbf	UL, ITB, cUL
4010250EG	1"	1130lbf	UL, cUL, ITB
4010250HD	11/16"	1130lbf	cUL, UL
4010300EG	1 1/8"	1130lbf	UL, cUL, ITB
4010300HD	7/8"	1130lbf	UL, cUL
4010350EG	1 5/16"	1130lbf	UL, cUL
4010400EG	1 3/8"	1130lbf	ITB, UL, cUL
4010400HD	1 3/4"	1130lbf	UL, cUL
4010500EG	1 5/8"	1430lbf	ITB, cUL, UL
4010600EG	1 7/8"	1940lbf	UL, ITB, cUL
4010800EG	3 1/8"	2000lbf	ITB, cUL, UL
4011000EG	2 9/16"	3600lbf	ITB
4011200EG	3 1/16"	3800lbf	ITB
4011400EG	4 3/8"	4200lbf	ITB

Catalog Number	C	Static Load (F)	Certifications
4011600EG	4 5/8"	4600lbf	ITB

Table 2/2			
Catalog Number	C	Static Load (F)	Certifications
4011800EG	5 1/8"	4800lbf	ITB
4012000EG	6"	4800lbf	ITB

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
 Option 1 – Customer Care
 Option 2 – Technical Support

Europe

Netherlands:
 +31 800-0200135
 France:
 +33 800 901 793

Europe

Germany:
 800 1890272
 Other Countries:
 +31 13 5835404

APAC

Shanghai:
 + 86 21 2412 1618/19
 Sydney:
 +61 2 9751 8500

