

410 Clevis Hanger, Light Duty



FEATURES

Recommended for the suspension of stationary non-insulated pipe lines

Also commonly used for the suspension of insulated pipe lines

Flared edges help prevent sharp surfaces from coming into contact with the pipe (1/2" to 8" pipe sizes)

Clevis bottom pivots to allow pipe to be fed from either direction

Conforms with Federal Specification WW-H-171 (Type 12), Manufacturers Standardization Society (MSS) SP-58 (Type 1)

Material: Steel
Finish: Electrogalvanized; Pregalvanized



SPECIFICATIONS


Table 1/2

Catalog Number	Pipe Size	Outer Diameter (OD)	Rod Size (RS)	A	B	C
4100050EG	1/2"	0.84"	3/8"	2 5/16"	1 1/8"	3/8"
4100075EG	3/4"	1.05"	3/8"	2 1/2"	1 1/4"	3/8"
4100100EG	1"	1.31"	3/8"	2 13/16"	1 3/8"	3/8"
4100125EG	1 1/4" Min	1.66"	3/8"	3 1/8"	1 9/16"	3/8"
4100150EG	1 1/2"	1.9"	3/8"	3 11/16"	2 1/16"	11/16"
4100200EG	2" Min	2 3/8"	3/8"	4 5/16"	2 1/2"	7/8"
4100250EG	2 1/2"	2 7/8"	1/2"	5 5/16"	3 1/16"	1"
4100300EG	3"	3 1/2"	1/2"	6 1/16"	3 1/2"	1 1/8"
4100400EG	4"	4 1/2"	5/8"	7 7/16"	4 3/8"	1 3/8"
4100500EG	5"	5 9/16"	5/8"	9 1/16"	5 1/8"	1 5/8"
4100600EG	6"	6 5/8"	3/4"	10 9/16"	6"	1 7/8"
4100800EG	8"	8 5/8"	3/4"	13 3/8"	7 9/16"	2 7/16"

Table 2/2

Catalog Number	Static Load (F)	Certifications
4100050EG	150lb	UL, cUL
4100075EG	150lb	UL, cUL
4100100EG	250lb	ITB, cUL, UL
4100125EG	250lb	ITB, UL, cUL
4100150EG	250lb	ITB, UL, cUL
4100200EG	250lb	UL, ITB, cUL
4100250EG	350lb	UL, ITB, cUL
4100300EG	350lb	ITB, UL, cUL
4100400EG	500lb	UL, ITB, cUL
4100500EG	600lb	UL, cUL, ITB
4100600EG	800lb	cUL, ITB, UL
4100800EG	1200lb	ITB, cUL, UL

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

