

510 nVent CADDY EZ Riser



The 510 nVent CADDY EZ Riser is a quick-closing pipe clamp, ideal for supporting vertical steel pipe where space is available. Ready-to-use out of the box, this solution has slotted holes to simplify assembly and eliminate loose hardware. Due to the serrated washer-head design, installers can easily assemble the EZ Riser with just a single tool.

FEATURES

Only one tool needed to tighten due to serrated washer-heads

Conforms with Federal Specification WW-H-171 (Type 8), Manufacturers Standardization Society (MSS) SP-58 (Type 8)

Material: Steel
Finish: Electrogalvanized



SPECIFICATIONS

Catalog Number	Pipe Size	Outer Diameter (OD)	Hole Size (HS)	A	B	Static Load (F)	Certifications
5100050EG	1/2"	0.84"	7/16"	8 1/2"	1"	255lb	
5100075EG	3/4"	1.05"	7/16"	9"	1"	255lb	
5100100EG	1"	1.31"	7/16"	9"	1"	255lb	
5100125EG	1 1/4" Min	1.66"	7/16"	9 7/16"	1"	255lb	
5100150EG	1 1/2"	1.9"	7/16"	9 7/8"	1"	255lb	
5100200EG	2" Min	2 3/8"	7/16"	10 1/4"	1 3/16"	255lb	ITB, UL, cUL
5100250EG	2 1/2"	2 7/8"	7/16"	11"	1 3/16"	390lb	cUL, ITB, UL
5100300EG	3"	3 1/2"	7/16"	11 3/4"	1 3/16"	530lb	UL, cUL, ITB
5100400EG	4"	4 1/2"	9/16"	13"	1 1/2"	810lb	cUL, ITB, UL
5100500EG	5"	5 9/16"	9/16"	14 1/2"	1 1/2"	1160lb	cUL, UL
5100600EG	6"	6 5/8"	9/16"	16"	2"	1570lb	cUL, UL
5100800EG	8"	8 5/8"	11/16"	18 1/4"	2"	2500lb	cUL, UL
5101000EG	10"	10 3/4"	11/16"	20 5/8"	2"	2500lb	



Catalog Number	Pipe Size	Outer Diameter (OD)	Hole Size (HS)	A	B	Static Load (F)	Certifications
5101200EG	12"	12 3/4"	11/16"	22 3/8"	2"	2700lb	
5101400EG	14"	14"	11/16"	24 1/8"	2"	2700lb	
5101600EG	16"	16"	13/16"	27 7/8"	2 1/2"	2900lb	

ADDITIONAL PRODUCT DETAILS

Clamp is fitted for steel pipe and should be installed below a coupling or shear lug, with bolts torqued to recommended value.

Slotted holes and bolts for pipe sizes up to 12" only.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

