


B18-Z Box/Conduit Hanger with Rod/Wire Clip



FEATURES

One assembly provides support for electrical box and/or conduit from drop wire or rod

Eliminates need for offset bending conduit

66% less Drop Wires (rod/wire application)

NEC® & CEC compliant

Increased capability and application options by combining 4Z and 6Z products into one enhanced and efficient offering

Improved multi-function clip allows for optimized inventory while reducing job site scheduling risks associated with multiple SKUs

Material: Spring Steel
Finish: nVent CADDY Armour



BABA



SPECIFICATIONS

Catalog Number	Flexible Conduit Size	MC/AC Cable Size	EMT Conduit Size	Outer Diameter	Rod Size	Wire Size
16MB18 			3/4", 1"	0.920" - 1.38"	1/4", 3/8"	#12
6MB18 	3/8"	14-2 to 12-3			1/4", 3/8"	#12
812MB18 			1/2", 3/4"	0.710" - 1.18"	1/4", 3/8"	#12
812MB188Z 			1/2", 3/4"	0.710" - 1.18"	1/2", 5/8"	#1

ADDITIONAL PRODUCT DETAILS

NEC® 300.11 requires dedicated drop wire/rod. For single and multiple runs of conduit.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

