

BC-M Conduit to Beam Clamp



FEATURES


- Easy installation to beam flanges
- Eliminates offset bending conduit
- Conduit clip rotates 360 degrees

Material: Spring Steel
Finish: nVent CADDY Armour



SPECIFICATIONS

Catalog Number	EMT Conduit Size	Rigid Conduit/Pipe Size	Outer Diameter (OD)	Flange Thickness (FT)	Torque (TQ)	Static Load (F)
BC16M	3/4", 1"	3/4", 1"	0.920" - 1.38"	1/2" Max	20 ft·lbf	100lb
BC20M	1 1/4"	1 1/4"		1/2" Max	20 ft·lbf	100lb
BC24M	1 1/2"	1 1/2"	1 1/2"	1/2" Max	20 ft·lbf	100lb
BC32M	2"	2"		1/2" Max	20 ft·lbf	100lb
BC812M	1/2", 3/4"	1/2", 3/4"	0.710" - 1.18"	1/2" Max	20 ft·lbf	100lb



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

