


BC26 Universal Beam Clamp with Tapped Hole



FEATURES

One thru-hole for easier installation of threaded rod

Conforms with Federal Specification WW-H-171 (Type 23), Manufacturers Standardization Society (MSS) SP-58 (Type 19 and 23)

SPECIFICATIONS

Table 1/2

Catalog Number	Material	Finish	Rod Size (RS)	Flange Thickness (FT)	A	Hole Size (HS)
BC260025EG	Cast Iron	Electrogalvanized	1/4"	13/16" Max	13/16"	1/4"

Table 2/2

Catalog Number	Hole Size (HS)	Hole Type	Screw Diameter (Sc)	Torque (TQ)	Static Load 1 (F1)	Static Load 2 (F2)
BC260025EG	1/4"	Threaded	1/4"	40 ft-lbf	250lb	100lb

ADDITIONAL PRODUCT DETAILS

Setscrew must be tightened and torqued onto the sloped side of the I-beam.



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

