

Cable/Conduit to Wire Clip

FEATURES

Supports cable and conduit without bending drop wire

Faster installation than traditional methods



Material: Spring Steel
Finish: nVent CADDY Armour



BABA




SPECIFICATIONS

Catalog Number	EMT Conduit Size	MC/AC Cable Size	Outer Diameter (OD)	Wire Size	Hole Size (HS)	Ultimate Static Load (F)	Certifications
PCS1 		14-2 to 10-3	0.450" - 0.6"	#12 - #8	1/4"	25lb	ITB, UL, cUL
PCS2 	1/2", 3/4"	10-3 to 6-3	0.600" - 0.9"	#12 - #8	1/4"	25lb	ITB

ADDITIONAL PRODUCT DETAILS

NEC® 300.11 requires dedicated drop wire/rod and EC311.



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

