

DOSR Double Offset Surge Restraint for CPVC Pipe



FEATURES

- Provides quick and easy snap-in installation of pipe
- Built-in nail tab allows for fast, temporary mounting to any surface
- Rated for use with CPVC fire sprinkler pipe
- Positions pipe 1-1/2" (38 mm) out and up from the mounting surface eliminating the need for wooden spacer blocks
- Meets the UL® 203 stringent upward thrust requirement
- UL® Listed as both a hanger and restraint in the double offset orientation
- Complies with static load requirements of NFPA® 13
- Includes mounting screws
- Can be used with 3TW backing nut on composite wood joist installations


Material: Steel
Finish: Pregalvanized



SPECIFICATIONS

Table 1/2						
Catalog Number	Pipe Size	Hole Size (HS)	Height (H)	Width (W)	Depth (D)	A
DOSR075	3/4"	0.2"	5.2"	1"	3 1/2"	1 1/2"
DOSR100	1"	0.2"	5.8"	1"	3.4"	1 1/2"

Table 2/2		
Catalog Number	Thickness (T)	Hanger Spacing
DOSR075	18ga	6' Max
DOSR100	18ga	6' Max



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

