

37 Steel Eye Socket Rod Hanger, 1/2" Rod, 2 1/2"–6" Pipe Size, FM, 2 1/2"–8" Pipe Size, UL

CATALOG NUMBER

0370050EG

FEATURES

Joins hanger rod to a structure



BABA



PRODUCT ATTRIBUTES

Material: Steel

Finish: Pregalvanized

Rod Size (RS): 1/2"

Pipe Size, FM: 2 1/2" - 6"

Pipe Size, UL: 2 1/2" - 8"

Hole Size 1 (HS1): 11/16"

Height (H): 2 3/4"

Width (W): 1 1/2"

Static Load (F): 760lbf

ADDITIONAL PRODUCT DETAILS

Load rating dependent on wood structure strength.

FM® Approved for 1/2" rod size when fastened to concrete and steel only.

DIAGRAMS

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

[nVent.com/ENDD1](https://www.nvent.com/ENDD1)

