

315 Malleable Iron Purlin Clamp, EG, 3/8" Rod, 1" Max Flange



CATALOG NUMBER

3150037EG

FEATURES

Attaches to lower flange of metal beams or purlins

Supports 45° flanges up to 2" long, and 90° flanges up to 1-1/2" high

Conforms with Federal Specification WW-H-171 (Type 23), Manufacturers Standardization Society ANSI®/MSS-SP-58 (Type 23)



PRODUCT ATTRIBUTES

Material: Cast Iron

Finish: Electrogalvanized

Rod Size (RS): 3/8"

Flange Thickness (FT): 1" Max

A: 2"

B: 1 1/2"

Screw Diameter (Sc): 3/8"

Torque (TQ): 5 ft-lbf


Pipe Size: 4" Max

Static Load (F): 400lbf

ADDITIONAL PRODUCT DETAILS

Setscrew must be tightened and torqued onto the sloped side of the I-beam.

Install in accordance with applicable code.



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

