

Combination Box/Conduit Hanger for 1/2-3/4" EMT with 512X

CATALOG NUMBER

812MB18XA

The nVent CADDY B18 Combination Box/Conduit Hanger for 512X presents an efficient and secure solution for the installation of electrical boxes and conduit in overhead applications by streamlining the process with a single-threaded rod drop. The notable scoreline breakaway feature allows for a tool-free installation by easily and safely snapping in half. The system is designed to provide greater efficiency in the field with our class-leading range of nVent CADDY Conduit Clamps.



FEATURES

Ideal means of support when used with the nVent CADDY 512X Electrical Box Mounting Clip (with offset)

One assembly provides support for horizontal electrical box and conduit from threaded rod

Eliminates need for offset bending conduit

Labor and time savings due to built-in first means of support and/or MC/AC cable

NEC® and CEC compliant



BABA



PRODUCT ATTRIBUTES

Finish: Pregalvanized;nVent CADDY Armour

Material: Steel;Spring Steel

EMT Conduit Size: 1/2";3/4"

Hole Size (HS): 1/4"

Hole Type: Plain


Screw Included: No

Length (L): 17 1/2"

Width (W): 2"

Depth (D): 3/4"

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

