


# Conduit Trapeze CCT125, 6 Number of Conduits, 14"



## CATALOG NUMBER

**CCT125X12**

The nVent CADDY Conduit Trapeze CCT125 range is a fast and cost-effective method to install larger branch circuits of conduit in overhead trapeze installations. The CCT125 series reduces installation time and material cost by eliminating the need for traditional fasteners, making it an ideal solution for contractors looking to maximize installation efficiency.

## FEATURES

Ideal for larger branch circuits

Accommodates 3/8" and 1/4" threaded rod trapeze drops

Up to 25% material savings over traditional methods

Reduces installation time up to 50%

Complies with UL® 2239



## PRODUCT ATTRIBUTES

Material: Steel

Finish: Pregalvanized

EMT Conduit Size: 1 1/4"

Rigid Conduit Size: 1 1/4"

Number of Conduits: 6

Rod Size (RS): 3/8"

Thickness (T): 16ga

Hole Size 1 (HS1): 0.44"

Hole Size 2 (HS2): 0.28"

Hole Size 3 (HS3): 0.12"

Hole Size 4 (HS4): 1.62"

Length 1 (L1): 12"

Length 2 (L2): 14"

Length 3 (L3): 2"

Length 4 (L4): 2"


## ADDITIONAL PRODUCT DETAILS

For 3/8" and 1/4" threaded rod trapeze drops, use washer or SN25 for 1/4" threaded rod applications.

The table contains maximum conduit size values.

| UL Load Rating                 |                     |                  |        |        |        |        |        |        |        |
|--------------------------------|---------------------|------------------|--------|--------|--------|--------|--------|--------|--------|
| Orientation                    | Mounting Fastener   | Fastener Spacing |        |        |        |        |        |        |        |
|                                |                     | 6"               | 12"    | 18"    | 24"    | 30"    | 36"    | 42"    | 48"    |
| Horizontal                     | 3/8" Threaded Rod   | 500 lb           | 500 lb | 400 lb | 300 lb | 275 lb | 250 lb | 225 lb | 200 lb |
|                                | 3/16" Shot-Fire Pin | 150 lb           | 125 lb | 100 lb | -      | -      | -      | -      | -      |
| Vertical                       | 3/8" Fastener       | 600 lb           | 600 lb | -      | -      | -      | -      | -      | -      |
| Evenly Distributed Load Rating |                     |                  |        |        |        |        |        |        |        |
| Horizontal                     | 3/8"                | -                | 750 lb | 600 lb | 475 lb | 425 lb | 375 lb | 325 lb | 300 lb |

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper

installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America**

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

**Europe**

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

**Europe**

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

**APAC**

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500

