

# nVent CADDY Pyramid Tool-Free Pipe Support Kit, 18.9"



## CATALOG NUMBER

**PTF16**

## FEATURES

Push-in clamps install without the need for additional tools or strut clamps

Ready to use out of the box, saving installation time and labor

Plastic clamps and base will not corrode pipe

Clamps come in two different sizes to fit project needs

Base includes multiple holes to accommodate a variety of clamp sizes and configurations

Additional clamps can be purchased separately for additional pipe runs

Foam bottom offers low abrasion interface for better roof membrane protection

Provides superior load distribution, even with varying rooftop surfaces

Compatible with roof surfaces including single ply, bituminous, metal and spray foam

Multiple sizes and load ratings offer the ability to tailor the solution to the application

Easy to transport to the roof

## PRODUCT ATTRIBUTES

Material: Polyethylene;Polypropylene;Nylon

Temperature: -50 to 150 °F

Static Load Safety Factor: 3:1

Length 1 (L1): 18.9"

Length 2 (L2): 7.99"

Length 3 (L3): 9.61"

Width (W): 7.91"

Height (H): 4.02"

A: 11.22"

B: 1.61"

Surface Area: 142in<sup>2</sup>

Unit Weight: 2 lb


Static Load (F): 1500lb


ADDITIONAL PRODUCT DETAILS

Length 2 represents maximum pipe center to pipe center using PTF2C clamps. Length 3 represents maximum pipe center to pipe center using PTF1C clamps.

| Tool-Free Pipe Clamp |                   |      |      |      |
|----------------------|-------------------|------|------|------|
| Part Number          | Outer Diameter OD | A    | B    | C    |
| PTF1C                | 0.50" – 1.32"     | 3/8" | 1.6" | 3/4" |
| PTF2C                | 0.84" – 2.38"     | 3/8" | 3.2" | 3/4" |

DIAGRAMS





## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.



[nVent.com/ENDDT](http://nVent.com/ENDDT) 3