


# Wire Basket Tray Round Wire 2"X6"X118", White, Pregalvanized



## CATALOG NUMBER

**WBT2X6WH**

The nVent CADDY Wire Basket Tray, Round Wire is a continuous pathway solution to support high-performance cabling systems while providing an ideal foundation for datacom and electrical contractors.

## FEATURES

Provides optimal support for high-performance data cable, up to and including Cat 5e, Cat 6, Cat 6A, Cat 7 and fiber optic

UL Classified as an equipment ground conductor, no field removal of paint required

T-Weld edge wire for cable and installer protection

Mill Certificates are available to document recycled content for possible LEED credits/certification



## PRODUCT ATTRIBUTES

Material: Steel

Finish: Pregalvanized

Color: White

Height (H): 2"


Width (W): 6

Length (L): 118"

Unit Weight: 9 lb

| 6" DEEP TRAY                                                                                                                   |            |
|--------------------------------------------------------------------------------------------------------------------------------|------------|
| Tray Size                                                                                                                      | Splice Qty |
| 6X8                                                                                                                            | 3          |
| 6X12                                                                                                                           | 3          |
| 6X16                                                                                                                           | 3          |
| 6X18                                                                                                                           | 4          |
| 6X20                                                                                                                           | 4          |
| 6X22                                                                                                                           | 4          |
| 6X24                                                                                                                           | 4          |
| 6X26                                                                                                                           | 5          |
| 6X28                                                                                                                           | 5          |
| 6X30                                                                                                                           | 5          |
| 6X32                                                                                                                           | 6          |
| 6X34                                                                                                                           | 6          |
| 6X36                                                                                                                           | 7          |
| These products are also available for Shaped Cable Tray and can be found by including an S to the end of any part number above |            |

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

#### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

#### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

#### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

