

ESC-M Conduit to Strut Clip

FEATURES

Attaches to open side of a strut channel

Includes easy close pipe and conduit clamp

Material: Spring Steel
Finish: nVent CADDY Armour



BABA




SPECIFICATIONS

Table 1/2

Catalog Number	EMT Conduit Size	Rigid Conduit/Pipe Size	MC/AC Cable Size	Flexible Conduit Size	Outer Diameter (OD)	Flange Thickness (FT)
ESC6M 		3/8"	14-2 to 12-3	3/8"	0.550" - 0.71"	3/8"
ESC812M 	1/2", 3/4"	1/2", 3/4"			0.710" - 1.18"	3/8"

Table 2/2

Catalog Number	Static Load (F)	Certifications
ESC6M 	25lb	
ESC812M 	25lb	cUL, UL



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

