

Four Hole External Coupler

FEATURES

Used to create metal frames with nVent CADDY Eristrut channels




SPECIFICATIONS

Table 1/2

Catalog Number	Material	Finish	Strut Type	Hole Size (HS)	Thickness (T)	A
U24A0000EG	Steel	Electrogalvanized	A (1 5/8" x 1 5/8")	9/16"	1/4"	7 1/4"

Table 2/2

Catalog Number	B	C
U24A0000EG	13/16"	1 7/8"



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500

