

H-MSM Conduit/Pipe to Flange Clip, Side Mount



FEATURES

Supports conduit/pipe or cable from beam flanges

Snap close clip pivots a full 360°

Requires only a hammer to install

Material: Spring Steel
Finish: nVent CADDY Armour



SPECIFICATIONS


Table 1/2

Catalog Number	EMT Conduit Size	Rigid Conduit/Pipe Size	Flexible Conduit Size	MC/AC Cable Size	Outer Diameter (OD)	Flange Thickness (FT)
16M24SM 	3/4", 1"	3/4", 1"			0.920" - 1.38"	1/8"
16M58SM 	3/4", 1"	3/4", 1"			0.920" - 1.38"	5/16" - 1/2"
16M912SM 	3/4", 1"	3/4", 1"			0.920" - 1.38"	9/16" - 3/4"
20M24SM 	1 1/4"	1 1/4"			1.380" - 1.65"	1/8"
20M58SM 	1 1/4"	1 1/4"			1.380" - 1.65"	5/16" - 1/2"
20M912SM 	1 1/4"	1 1/4"			1.380" - 1.65"	9/16" - 3/4"
24M24SM 	1 1/2"	1 1/2"			1.650" - 1.97"	1/8"
24M58SM 	1 1/2"	1 1/2"			1.650" - 1.97"	5/16" - 1/2"
24M912SM 	1 1/2"	1 1/2"			1.650" - 1.97"	9/16" - 3/4"
32M24SM 	2"	2"			1.970" - 2.36"	1/8"

Catalog Number	EMT Conduit Size	Rigid Conduit/Pipe Size	Flexible Conduit Size	MC/AC Cable Size	Outer Diameter (OD)	Flange Thickness (FT)
32M58SM 	2"	2"			1.970" - 2.36"	5/16" - 1/2"
32M912SM 	2"	2"			1.970" - 2.36"	9/16" - 3/4"
6M24SM 		3/8"	3/8"	14-2 to 12-3	0.550" - 0.71"	1/8"
6M58SM 		3/8"	3/8"	14-2 to 12-3	0.550" - 0.71"	5/16" - 1/2"
6M912SM 		3/8"	3/8"	14-2 to 12-3	0.550" - 0.71"	9/16" - 3/4"
812M24SM 	1/2", 3/4"	1/2", 3/4"			0.710" - 1.18"	1/8"
812M58SM 	1/2", 3/4"	1/2", 3/4"			0.710" - 1.18"	5/16" - 1/2"
812M912SM 	1/2", 3/4"	1/2", 3/4"			0.710" - 1.18"	9/16" - 3/4"

Table 2/2

Catalog Number	Static Load (F)	Certifications
16M24SM 	25lb	UL, cUL
16M58SM 	25lb	cUL, UL
16M912SM 	25lb	cUL, UL
20M24SM 	25lb	UL, cUL
20M58SM 	25lb	
20M912SM 	25lb	
24M24SM 	25lb	UL, cUL
24M58SM 	25lb	UL, cUL
24M912SM 	25lb	UL, cUL
32M24SM 	25lb	cUL, UL
32M58SM 	25lb	cUL, UL
32M912SM 	25lb	UL, cUL
6M24SM 	25lb	cUL, UL
6M58SM 	25lb	UL, cUL
6M912SM 	25lb	
812M24SM 	25lb	ITB, cUL, UL
812M58SM 	25lb	cUL, ITB, UL
812M912SM 	25lb	cUL, UL, ITB



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

