


Hammer-On Flange Clip, Side Mount

FEATURES

Provides an attachment for wire, S-hooks, chain, nVent CADDY Speed Link or other assemblies to flanges and profiles

Fits most beams

Installs with just a hammer




SPECIFICATIONS

Catalog Number	Material	Finish	Flange Thickness (FT)	Hole Size (HS)	Static Load (F)	Certifications
2H4 	Spring Steel	nVent CADDY Armour	3/32" - 9/64"	1/4"	160lb	ITB, UL, cUL
4H1318 	Spring Steel	nVent CADDY Armour	13/16" - 1 1/8"	1/4"	200lb	cUL, UL
4H24 	Spring Steel	nVent CADDY Armour	1/8" - 1/4"	1/4"	200lb	cUL, UL, CE, 4H, EM, EBC, ITB
4H24SS 	Stainless Steel 301 (EN 1.4310)		1/8"	1/4"	140lb	
4H58 	Spring Steel	nVent CADDY Armour	5/16" - 1/2"	1/4"	200lb	UL, CE, 4H, EM, EBC, cUL, ITB
4H58SS 	Stainless Steel 301 (EN 1.4310)		5/16" - 1/2"	1/4"	140lb	
4H912 	Spring Steel	nVent CADDY Armour	9/16" - 3/4"	1/4"	200lb	cUL, UL, CE, 4H, EM, EBC, ITB

Catalog Number	Material	Finish	Flange Thickness (FT)	Hole Size (HS)	StaticLoad (F)	Certifications
4H912SS 	Stainless Steel 301 (EN 1.4310)		9/16" - 3/4"	1/4"	140lb	

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

