

Improved nVent CADDY Cat HP J-Hook Mod Clip with Pedestal Clamp



Improved nVent CADDY Cat HP Mod Clip J-Hook with Pedestal Clamp simplifies installation to pedestals under raised floors. Enjoy enhanced stability and customization for efficient cable management while gaining ultimate flexibility on the job and minimizing inventory impact.

FEATURES

Listed for use with flexible conduit, cable, or tubing

Requires no screws, rivets or special tools for assembly

Works with nVent J-Hook Versa-Mount technology from nVent CADDY


Finish: Electrogalvanized;nVent CADDY Armour

Material: Steel;Spring Steel



SPECIFICATIONS

Catalog Number	Pedestal Size	Static Load (F)
CATHPMCD0B	3/4" Round	
CATHPMCD1B	3/4" Square, 7/8" - 1 1/8" Round	15.74lb
CATHPMCD2.5B	1" Square	
CATHPMCD2B	7/8" Square	
CATHPMCD3B	1 1/2" Round	



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

