


MC/AC Cable to Flange Clip, Side Mount



FEATURES

No tools required for installation

Compliant with NEC® Article 300.4(d), allowing cable to be positioned a minimum of 1-1/4" from face of stud

Compliant with CEC Rule 12-618 for support of MC/AC cable

Material: Spring Steel
Finish: nVent CADDY Armour



BABA




SPECIFICATIONS

Catalog Number	Flange Thickness (FT)	MC/AC Cable Size	Outer Diameter (OD)
MAC224SM 	1/8"	14-2 to 10-3	0.6" Max
MAC258SM 	5/16" - 1/2"	14-2 to 10-3	0.6" Max
MAC2912SM 	9/16" - 3/4"	14-2 to 10-3	0.6" Max

ADDITIONAL PRODUCT DETAILS

Assemblies allow for support from most main and substructures.



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

