

MC/AC Cable Support Bracket with Rod/Wire Clip



FEATURES

Neatly isolates, supports and secures MC/AC cables

Properly spaces MC/AC cable to help eliminate bundling and NEC® & CEC derating issues

Results in a "neat and workmanlike" installation

Increased capability and application options by combining 4Z and 6Z products into one enhanced and efficient offering

Improved multi-function clip allows for optimized inventory while reducing job site scheduling risks associated with multiple SKUs

Material: Steel
Finish: Electrogalvanized



BABA



SPECIFICATIONS

Table 1/2


Catalog Number	Isolated Ground Cable Size	MC/AC Cable Size	Super Neutral Cable Size	Cable Capacity	Rod Size (RS)	Wire Size
MCS1004Z 		14-3 to 10-2	10-2	8	1/4", 5/16", 3/8"	#12 - #8
MCS1008Z 		14-3 to 10-2	10-2	8	1/2", 5/8"	#1
MCS1014Z 	12-3 to 8-2	10-3 to 8-3	12-3 to 10-2	7	1/4", 5/16", 3/8"	#12 - #8
MCS504Z 		14-3 to 10-2	10-2	4	1/4", 5/16", 3/8"	#12 - #8

Table 2/2

Catalog Number	Flange Thickness (FT)	Outer Diameter (OD)
MCS1004Z 	0.1250" - 0.4375"	0.430" - 0.56"

Catalog Number	Flange Thickness (FT)	Outer Diameter (OD)
MCS1008Z 		0.430" - 0.56"
MCS1014Z 	0.1250" - 0.4375"	0.560" - 0.69"
MCS504Z 	0.1250" - 0.4375"	0.430" - 0.56"

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

nVent.com/GRDDT

