

Multi-Function Clip



FEATURES

Provides attachment of electrical boxes

Supports #10-24 and 1/4-20 (M6) threaded bridle rings

Installs more confidence installing conduit, MC/AC, and low voltage applications

Material: Spring Steel
Finish: nVent CADDY Armour



BABA



SPECIFICATIONS

Table 1/2

Catalog Number	Rod Size (RS)	Wire Size	Flange Thickness (FT)	Hole Size (HS)	Screw Included	Screw Diameter (Sc)
4Z34 	1/4", 5/16", 3/8"	#12 - #8	1/8" - 3/8"	1/4"	No	
4Z4S 	1/4", 5/16", 3/8"	#12 - #8	1/8" - 3/8"		Yes	1/4"
8Z34 	1/2", 5/8"	#1		1/4"	No	
8Z4S 	1/2", 5/8"	#1			Yes	1/4"


Table 2/2

Catalog Number	Screw Diameter (Sc)	Static Load 1 (F1)	Static Load 2 (F2)	Certifications
4Z34 		25lb	20lb	ITB, UL, cUL
4Z4S 	1/4"	25lb	20lb	cUL, UL
8Z34 			50lb	cUL, UL
8Z4S 	1/4"		50lb	cUL, UL

ADDITIONAL PRODUCT DETAILS

NEC® 300.11 requires dedicated drop wire/rod and EC311.

4Z parts installed on 3/8" (M10) smooth rod in the F2 direction has a Static Load Rating of 15 lb (67 N).



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

