

nVent CADDY All-in-One Floor-Mounted With Removable Mud Ring



FEATURES

Preset to a finish height of 18 in from the floor (adjustable to 12 or 15 in)

Removable mud ring provides front access to the interior of the box

Box remains fixed in place when mud ring is removed

Integrated first means of support accepts conduit or MC/AC cable

Accommodates additional nVent CADDY All-in-One box assemblies, support brackets and low-voltage mounting plates

Includes multiple 1/2 and 3/4 in knockouts on each side of the box



SPECIFICATIONS

Table 1/2

Catalog Number	Material	Finish	EMT Conduit Size	MC/AC Cable Size	Knockout Sizes	Gang
A1FF1G	Steel	Pregalvanized	1/2", 3/4"	14-2 to 12-3	(8) 1/2", 3/4", (3) 1/2"	1


Table 2/2

Catalog Number	Ground Wire Included	Box Volume	Drywall Thickness	Depth (D)	A	B	C
A1FF1G	Yes	32.8in ³	5/8"	3 5/8"	22 3/16"	7 3/4"	2 11/16"

ADDITIONAL PRODUCT DETAILS

Ground wire pigtail is 10".

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

