


nVent CADDY All-in-One Stud-Mounted With Removable Mud Ring



FEATURES

Removable mud ring provides front access to the interior of the box

Box remains fixed in place when mud ring is removed

Includes multiple knockouts on each side of the box

Assemblies keyed for precise alignment when installed on both sides of a stud

Material: Steel
Finish: Pregalvanized



SPECIFICATIONS

Table 1/2

Catalog Number	Knockout Sizes	Gang	Ground Wire Included	Back Plate Pre-assembled	Box Volume	Drywall Thickness
A1SD1N	(5) 1/2", 3/4", (1) 1 1/2", (3) 1"	1	No	Yes	32.8in ³	5/8"
A1SF1G	(8) 1/2", 3/4"	1	Yes	Yes	32.8in ³	5/8"
A1SF2G	(8) 1/2", 3/4"	2	Yes	Yes	32.8in ³	5/8"


Table 2/2

Catalog Number	Depth (D)	A	B
A1SD1N	3 5/8"	5 3/4"	5 1/8"
A1SF1G	3 5/8"	5 3/4"	5 1/8"
A1SF2G	3 5/8"	5 3/4"	5 1/8"

ADDITIONAL PRODUCT DETAILS

Ground wire pigtail is 10".

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

