


nVent CADDY BCSP Box/Conduit Securement Platform, Multifunction



The nVent CADDY Box/Conduit Securement Platform (BCSP) Multifunction is a fast and secure method to install a wide range of junction and multiple electrical boxes/conduit in overhead installations with a single-threaded rod drop. Our improved product is ideal for open ceiling environments with limited access to the structure (high ceilings). The nVent CADDY BCSP Multifunction is designed to simplify electrical box and conduit installation compared to traditional methods that include multiple connection points and supports, eliminating the need for additional hardware while offering easy, tool-free installation. Our solution provides flexibility on the job by accommodating various sizes and combinations while allowing for simple, repeated installation due to its self-alignment features.

FEATURES

Designated hole pattern for multiple box array

Accommodates a wide range of electrical boxes

Tool-free conduit securement options

Up to 50% installation time savings over traditional methods

Supports electrical boxes in 16 in stud spacing




SPECIFICATIONS

Table 1/2

Catalog Number	Material	Finish	Box Size	Rod Size (RS)	Multiple Box	Height (H)
BCSP612F	Steel	Pregalvanized	6", 8", 10", 12"	0.375"	Yes	0.5"

Table 2/2

Catalog Number	Width (W)	Thread Size (TS)	Hole Size 1 (HS1)	Hole Size 2 (HS2)
BCSP612F	18"	1/4" UNC	0.1"	0.3"



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

