

nVent CADDY Cablecat J-Hook with Hammer-On Flange Clip



FEATURES

Hammer-on beam clamp with attached nVent CADDY Cablecat J-Hook

Supports low voltage cables

Material: Steel;Spring Steel
Finish: Pregalvanized;nVent CADDY Armour




BABA



SPECIFICATIONS

Catalog Number	Diameter (Ø)	Flange Thickness (FT)
CAT1224SM 	3/4"	1/8"
CAT12912SM 	3/4"	9/16" - 3/4"
CAT1258SM 	3/4"	5/16" - 1/2"



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

