


# nVent CADDY Cable/Conduit Stud Attachment, Multifunction



The nVent CADDY Cable/Conduit Stud Attachment, Multifunction is a simplified, easy-to-use solution for mounting both EMT and flexible conduit above electrical boxes. Its universal design eliminates the need to carry multiple parts on the job and allows contractors to utilize just one fastener. Additionally, the Cable/Conduit Stud Attachment, Multifunction increases functionality by featuring a wider bracket to span across the entirety of the electrical box and reach all three knockouts. Whether you're securing EMT, flexible conduit or both, rest assured, this simple solution improves productivity while keeping your job site safe.

## FEATURES


- Multifunction design allows for different securement combinations such as one EMT and up to two flexible conduit cables or three conduit cables
- Capable of securing EMT sizes spanning from ½ to 1 in
- Score marks to break off excess bracket
- Compliant with NEC® Article 358.30(A), which requires conduit support within 36 in of an electrical box
- Compliant with CEC Rule 12-1404, which requires conduit support within 1 m of an electrical box
- Compliant with CEC Rule 12-618, which requires support of armored cable within 300 mm (12 in) of an electrical box



## SPECIFICATIONS

| Table 1/2      |          |                    |                  |                  |                        |                        |
|----------------|----------|--------------------|------------------|------------------|------------------------|------------------------|
| Catalog Number | Material | Finish             | EMT Conduit Size | MC/AC Cable Size | Outer Diameter 1 (OD1) | Outer Diameter 2 (OD2) |
| CS816M         | Steel    | nVent CADDY Armour | 0.5" - 1"        | 14-2 to 2-3      | 0.5" Max               | 0.5" Max               |

| Table 2/2      |                     |           |
|----------------|---------------------|-----------|
| Catalog Number | Outer Diameter (OD) | Box Depth |
| CS816M         | 0.500" - 1.163"     | 2.125"    |



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500

