

nVent CADDY Pyramid Crossover Ladder, 50°



FEATURES

Standard angle ladders provide easy changes in elevation

Interchangeable components are easily assembled yielding labor-saving and quick installations

nVent CADDY Pyramid bases provide superior load distribution and roof membrane compatibility

Foam bottom offers low abrasion interface for better roof membrane protection

Aluminum construction designed to withstand harsh environments

Walking surfaces with serrated tread provides maximum slip resistance and drainage

Compliant with OSHA, Cal/OSHA and ANSI® standards

Material: Aluminum;Polypropylene;Polyethylene



SPECIFICATIONS

Catalog Number	Walkway Height	Number of Steps	Height (H)	Width (W)	Depth (D)	A	Static Load (F)
PCL50S2	20"	2	62"	52.4"	22.9"	9 1/2"	500lbf
PCL50S3	30"	3	72"	52.4"	36.1"	9 1/2"	500lbf
PCL50S4	40"	4	82"	52.4"	44 1/2"	9 1/2"	500lbf
PCL50S5	50"	5	92"	52.4"	52.9"	9 1/2"	500lbf
PCL50S6	60"	6	102"	52.4"	61.3"	9 1/2"	500lbf

ADDITIONAL PRODUCT DETAILS

Clearance of walkway is 3" less than the walkway height.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

