

# nVent CADDY Speed Link SLC with Decking Hook



The nVent CADDY Speed Link SLC with Decking Hook delivers a fast, dependable way to suspend duct from hollow metal decking, helping crews move quickly and reduce time on elevated surfaces. Offered in three cable lengths to cover a wide range of applications, the Speed Link SLC with Decking Hook helps reduce on-site measuring and rework by giving installers a ready-to-use solution. The tool-free locking device design makes adjustment simple and flexible when working with unknown structures or changing field conditions. Leveling and final positioning can be done quickly without specialized tools, ensuring contractors spend less time installing and more time finishing the job.

## FEATURES

Includes wire and is assembled to a decking hook end fitting

Quickly and easily attaches to hollow metal decking

Spring-loaded ends snap into decking hole and lock into place

Innovative design helps protect the wire from sharp edges of decking hole, minimizing risk of damage to wire

Compatible with nVent CADDY Speed Link SLS Locking Device and the nVent CADDY SLK Locking Device in 2mm and 3mm sizes (sold separately)

|                                   |                   |
|-----------------------------------|-------------------|
| <b>Material:</b>                  | Steel             |
| <b>Finish:</b>                    | Electrogalvanized |
| <b>Static Load Safety Factor:</b> | 5:1               |
| <b>Complies With:</b>             | SMACNA HVAC-DCS   |

## SPECIFICATIONS

| Catalog Number | Wire Rope Diameter | Wire Rope Length | Roof Decking Sheet Thickness | A     | Hole Size (HS) | Static Load (F) |
|----------------|--------------------|------------------|------------------------------|-------|----------------|-----------------|
| SLC2L10DH      | 2 mm               | 32.8'            | 16 ga                        | 0.36" | 0.32"          | 100lbf          |
| SLC2L5DH       | 2 mm               | 16.4'            | 16 ga                        | 0.36" | 0.32"          | 100lbf          |
| SLC2L3DH       | 2 mm               | 9.9'             | 16 ga                        | 0.36" | 0.32"          | 100lbf          |

| Catalog Number | Wire Rope Diameter | Wire Rope Length | Roof Decking Sheet Thickness | A     | Hole Size (HS) | Static Load (F) |
|----------------|--------------------|------------------|------------------------------|-------|----------------|-----------------|
| SLC15L10DH     | 1.5 mm             | 32.8'            | 16 ga                        | 0.36" | 0.32"          | 44lbf           |
| SLC15L3DH      | 1.5 mm             | 9.9'             | 16 ga                        | 0.36" | 0.32"          | 44lbf           |
| SLC15L5DH      | 1.5 mm             | 16.4'            | 16 ga                        | 0.36" | 0.32"          | 44lbf           |

DIAGRAMS

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500

