

nVent CADDY Speed Link SLC with Hook



The nVent CADDY Speed Link SLC with Hook delivers a fast, dependable way to suspend duct from building structures or hanging services, helping crews move quickly and reduce time on elevated surfaces. Offered in three cable lengths to cover a wide range of applications, the Speed Link SLC with Hook helps reduce on-site measuring and rework by giving installers a ready-to-use solution. The tool-free locking device design makes adjustment simple and flexible when working with unknown structures or changing field conditions. Leveling and final positioning can be done quickly without specialized tools, ensuring contractors spend less time installing and more time finishing the job.

FEATURES

Includes wire and is assembled to a hook end fitting

Quickly and easily attaches to hanging services and building structures

Hooks to a wide range of nVent CADDY fasteners

Fastens to the building structure or hanging services by looping around and hooking to wire rope

Easy to remove for applications requiring maintenance

Spring latch helps provide a secure connection

Compatible with nVent CADDY Speed Link SLS Locking Device and nVent CADDY SLK Locking Device in 2mm and 3mm sizes (sold separately)

Material:	Steel
Finish:	Electrogalvanized
Static Load Safety Factor:	5:1
Complies With:	SMACNA HVAC-DCS


SPECIFICATIONS

Catalog Number	Wire Rope Diameter	Wire Rope Length	A	B	C	Static Load (F)
SLC2L10N	2 mm	32.8'	2.24"	0.87"	0.22"	100lbf
SLC2L3N	2 mm	9.9'	2.24"	0.87"	0.22"	100lbf

Catalog Number	Wire Rope Diameter	Wire Rope Length	A	B	C	Static Load (F)
SLC2L5N	2 mm	16.4'	2.24"	0.87"	0.22"	100lbf
SLC3L10N	3 mm	32.8'	2.27"	0.91"	0.24"	200lbf
SLC3L3N	3 mm	9.9'	2.27"	0.91"	0.24"	200lbf
SLC3L5N	3 mm	16.4'	2.27"	0.91"	0.24"	200lbf
SLC15L10N	1.5 mm	32.8'	1.89"	0.71"	0.18"	44lbf
SLC15L3N	1.5 mm	9.9'	1.89"	0.71"	0.18"	44lbf
SLC15L5N	1.5 mm	16.4'	1.89"	0.71"	0.18"	44lbf

Height (H): 2.15"

Width (W): 3/4"



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

