

nVent CADDY Speed Link SLK with Angle Bracket



FEATURES

Complete system includes wire, locking device and pre-assembled angle bracket end fitting

Ideal for attaching to concrete, steel or wood surfaces

Simple alternative to jack chain and additional hardware

Material: Steel;Zinc Alloy;Polypropylene
Finish: Electrogalvanized
Static Load Safety Factor: 5:1
Complies With: SMACNA HVAC-DCS



SPECIFICATIONS


Table 1/2

Catalog Number	Wire Rope Diameter	Wire Rope Length	A	Hole Size (HS)	Height (H)	Width (W)
SLK15L1AB	1.5 mm	3.3'	0.89"	0.28"	2.15"	3/4"
SLK15L2AB	1.5 mm	6.6'	0.89"	0.28"	2.15"	3/4"
SLK15L3AB	1.5 mm	9.9'	0.89"	0.28"	2.15"	3/4"
SLK15L5AB	1.5 mm	16.4'	0.89"	0.28"	2.15"	3/4"
SLK2L2AB	2 mm	6.6'	0.89"	0.28"	2.15"	3/4"
SLK2L3AB	2 mm	9.9'	0.89"	0.28"	2.15"	3/4"
SLK2L5AB	2 mm	16.4'	0.89"	0.28"	2.15"	3/4"
SLK3L10AB	3 mm	32.8'	0.89"	0.28"	2 1/2"	0.9"
SLK3L5AB	3 mm	16.4'	0.89"	0.28"	2 1/2"	0.9"
SLK3L7AB	3 mm	22.9'	0.89"	0.28"	2 1/2"	0.9"

Table 2/2

Catalog Number	Thickness (T)	Angle (a)	Static Load (F)	Certifications
SLK15L1AB	1/2"	90 ° Max	44lbf	cUL, UL, ITB
SLK15L2AB	1/2"	90 ° Max	44lbf	cUL, UL, ITB
SLK15L3AB	1/2"	90 ° Max	44lbf	cUL, UL, ITB
SLK15L5AB	1/2"	90 ° Max	44lbf	ITB, cUL, UL
SLK2L2AB	1/2"	90 ° Max	100lbf	ITB, cUL, UL
SLK2L3AB	1/2"	90 ° Max	100lbf	cUL, ITB, UL
SLK2L5AB	1/2"	90 ° Max	100lbf	UL, cUL, ITB
SLK3L10AB	0.6"	90 ° Max	200lbf	
SLK3L5AB	0.6"	90 ° Max	200lbf	
SLK3L7AB	0.6"	90 ° Max	200lbf	

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

