

nVent CADDY Speed Link SLK with Hammer-On Flange Clip



FEATURES

Complete system includes wire, locking device and pre-assembled nVent CADDY Hammer-On Flange Clip end fitting

Installs with just a hammer

Fits most beams

Material: Steel;Polypropylene;Zinc Alloy
Finish: Electrogalvanized
Static Load Safety Factor: 5:1
Complies With: SMACNA HVAC-DCS



SPECIFICATIONS

Catalog Number	Wire Rope Diameter	Wire Rope Length	Flange Thickness (FT)	Static Load (F)
SLK15L34H24	1.5 mm	9.9'	1/8"	44lbf
SLK15L34H58	1.5 mm	9.9'	5/16" - 1/2"	44lbf
SLK2L34H24	2 mm	9.9'	1/8"	100lbf
SLK2L34H58	2 mm	9.9'	5/16" - 1/2"	100lbf

Height (H): 2.15"
Width (W): 3/4"
Thickness (T): 1/2"
Angle (a): 90 ° Max



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

