

nVent CADDY Speed Link SLK with Toggle



FEATURES

Complete system includes wire, locking device and pre-assembled toggle end fitting

Attaches to clearance holes in a variety of structures or hanging devices

Ideal for supporting lighting fixtures

Also available in Y-toggle configuration

Material: Steel;Zinc Alloy;Polypropylene
Finish: Electrogalvanized
Static Load Safety Factor: 5:1
Complies With: SMACNA HVAC-DCS
Wire Rope Diameter: 1.5 mm




SPECIFICATIONS

Catalog Number	Wire Rope Length	A	B	Static Load (F)
SLK15L10T	32.8'	1.54"	0.2"	44lbf
SLK15L1T	3.3'	1.54"	0.2"	44lbf
SLK15L1TR2	3.3'	1.54"	0.2"	44lbf
SLK15L2T	6.6'	1.54"	0.2"	44lbf
SLK15L2TR2	6.6'	1.54"	0.2"	44lbf
SLK15L3T	9.9'	1.54"	0.2"	44lbf
SLK15L3TR2	9.9'	1.54"	0.2"	44lbf
SLK15L5T	16.4'	1.54"	0.2"	44lbf
SLK15L7T	22.9'	1.54"	0.2"	44lbf

Height (H): 2.15"
Width (W): 3/4"
Thickness (T): 1/2"

Angle (a): 90 ° Max

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

