

nVent CADDY Speed Link SLK with Y-Hook



FEATURES

Complete system includes wire, locking device and two pre-assembled hook end fittings

Fastens to the building structure and hooks to hanging services and tray

Spring latch helps provide secure connection

Convenient design allows one hook to be temporarily detached for maintenance or to add cables to the tray

Single drop with double hook provides increased stability to the system

Also available in a single-hook end fitting configuration


Material: Steel;Zinc Alloy;Polypropylene
Finish: Electrogalvanized
Static Load Safety Factor: 5:1
Complies With: SMACNA HVAC-DCS
Wire Rope Diameter: 2 mm



SPECIFICATIONS

Catalog Number	Wire Rope Length	Wire Rope "Y" Length (YL)	A	B	C	Static Load (F)
SLK2YH500L2	6.6'	19.6"	2.3"	0.9"	1/4"	100lbf
SLK2YH500L2R2	6.6'	19.6"	2.3"	0.9"	1/4"	100lbf
SLK2YH500L3	9.9'	19.6"	2.3"	0.9"	1/4"	100lbf
SLK2YH500L3R2	9.9'	19.6"	2.3"	0.9"	1/4"	100lbf
SLK2YH500L7	22.3'	19.6"	2.3"	0.9"	1/4"	100lbf

Height (H): 2.15"
Width (W): 3/4"
Thickness (T): 1/2"
Angle (a): 90 ° Max



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

