


PH Multi-Purpose Purlin Clamp



FEATURES

Attaches to bottom of purlins and beams to support threaded rod

Material: Steel
Finish: Electrogalvanized




SPECIFICATIONS

Catalog Number	Rod Size (RS)	Flange Thickness (FT)	B	Torque (TQ)	Static Load 1 (F1)	Static Load 2 (F2)	Nut Included
PH4	1/4"	1/4" Max	3/4" Min	30 ft·lbf	200lb	160lb	No
PH6	3/8"	1/4" Max	3/4" Min	30 ft·lbf	200lb	160lb	No
PH6FP	3/8"	1/4" Max	3/4" Min	30 ft·lbf	200lb		Yes

ADDITIONAL PRODUCT DETAILS

A jam nut is required for fire protection applications.

Refer to Static Load 1 when attaching to C and Z purlins. Refer to Static Load 2 when attaching to a flat flange.



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

