

Push In Conduit to Conduit Clamp



FEATURES

Ideal as spacer between same or different size conduit

No tools required for installation


Top conduit to be used for support only, not a raceway

Material: Spring Steel
Finish: nVent CADDY Armour



SPECIFICATIONS

Catalog Number	EMT Conduit Size 1	EMT Conduit Size 2	Rigid Conduit Size 1	Rigid Conduit Size 2	Outer Diameter 1 (OD1)	Outer Diameter 2 (OD2)	Ultimate Static Load (F)
12P12P 	3/4"	3/4"	1/2"	1/2"	0.870" - 1.18"	0.870" - 1.18"	25lb
12P16P 	3/4"	1"	1/2"	3/4"	0.870" - 1.18"	1.180" - 1.38"	25lb
16P16P 	1"	1"	3/4"	3/4"	1.180" - 1.38"	1.180" - 1.38"	25lb
8P12P 	1/2"	3/4"		1/2"	0.710" - 0.87"	0.870" - 1.18"	25lb
8P8P 	1/2"	1/2"			0.710" - 0.87"	0.710" - 0.87"	25lb



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

