

Snap Close Conduit to Conduit Clamp



FEATURES

Fast and easy assembly for lightweight loads

No screws or bolts required

Material: Spring Steel
Finish: nVent CADDY Armour



BABA



SPECIFICATIONS

Table 1/2

Catalog Number	EMT Conduit Size 1	EMT Conduit Size 2	Flexible Conduit Size	MC/AC Cable Size	Outer Diameter 1	Outer Diameter 2
1616M 	3/4", 1"	3/4", 1"			0.920" - 1.38"	0.920" - 1.38"
166M 	3/4", 1"	3/8"	3/8"	14-2 to 12-3	0.920" - 1.38"	0.550" - 0.71"

Table 2/2

Catalog Number	Ultimate Static Load	Certifications
1616M 	100lb	cUL, UL
166M 	100lb	

ADDITIONAL PRODUCT DETAILS

For 14-2 through 12-3 MC/AC cable, use part 166M.

Total load of trapeze must not exceed 100 lb.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

