

Snap Close Conduit/Pipe Clamp



The nVent CADDY Snap Close Conduit Clamps (M-Series) are a fast and efficient method to secure conduit branch circuits for electrical installations. The M-Series is designed to provide positional consistency in application by eliminating conduit offset as well as maintain spacing entering electrical boxes. Increase installation efficiency by utilizing our comprehensive conduit range for your next electrical project.

FEATURES

May be used for either vertical or horizontal installations

Eliminates need for offset bending conduit

Finger closure, no tools required

Locking design has greater resistance to twisting loads and is stronger than any on the market

Low profile locking tabs and smooth gripping dimples remove the possibility of scrapes

812M and 16M feature double tabs to center conduit, increase range and holding power and prevent conduit from sliding

Material: Spring Steel
Finish: nVent CADDY Armour



BABA



SPECIFICATIONS

Table 1/2



Catalog Number	Flexible Conduit Size	MC/AC Cable Size	EMT Conduit Size	Rigid Conduit/Pipe Size	Outer Diameter (OD)	Hole Size (HS)
16M 			3/4", 1"	3/4", 1"	0.920" - 1.38"	9/32"
16M4I 			3/4", 1"	3/4", 1"	0.920" - 1.38"	1/4"
20M 			1 1/4"	1 1/4"	1.380" - 1.65"	9/32"
20M4I 			1 1/4"	1 1/4"	1.380" - 1.65"	1/4"

Catalog Number	Flexible Conduit Size	MC/AC Cable Size	EMT Conduit Size	Rigid Conduit/Pipe Size	Outer Diameter (OD)	Hole Size (HS)
24M 			1 1/2"	1 1/2"	1.650" - 1.97"	9/32"
24M4I 			1 1/2"	1 1/2"	1.650" - 1.97"	1/4"
32M 			2"	2"	1.970" - 2.36"	9/32"
32M4I 			2"	2"	1.970" - 2.36"	1/4"
6M 	3/8"	14-2 to 12-3			0.550" - 0.71"	9/32"
6M4I 	3/8"	14-2 to 12-3			0.550" - 0.71"	1/4"
812M 			1/2", 3/4"	1/2", 3/4"	0.710" - 1.18"	9/32"
812M4I 			1/2", 3/4"	1/2", 3/4"	0.710" - 1.18"	1/4"

Table 2/2

Catalog Number	Hole Type	Static Load 1 (F1)	Static Load 2 (F2)
16M 	Plain	100lb	25lb
16M4I 	Threaded	100lb	25lb
20M 	Plain	100lb	25lb
20M4I 	Threaded	100lb	25lb
24M 	Plain	100lb	25lb
24M4I 	Threaded	100lb	25lb
32M 	Plain	100lb	25lb
32M4I 	Threaded	100lb	25lb
6M 	Plain	100lb	25lb
6M4I 	Threaded	100lb	25lb
812M 	Plain	100lb	25lb
812M4I 	Threaded	100lb	25lb

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

