

Strut Nut without Spring

FEATURES

Used to create metal frames with nVent CADDY Eristrut channels



Material: Steel
Finish: Electrogalvanized
Static Load Safety Factor: 3:1





SPECIFICATIONS

Catalog Number	Rod Size (RS)	Thickness (T)	Torque (TQ)	Certifications
NUT0025EG	1/4"	1/4"	6 ft·lbf	
NUT0037EG	3/8"	3/8"	19 ft·lbf	
NUT0050EG	1/2"	1/2"	50 ft·lbf	OSHDP/HCAI

Pull-Out Strength			
Part Number	Channel Type	Channel Thickness	
		12 GA	14 GA
NUT0025xx	A, C	450 lb	450 lb
	D, E	450 lb	-
NUT0037xx	A, C	1,100 lb	1,000 lb
	D, E	1,100 lb	-
NUT0050xx	A	2,000 lb	1,400 lb
	D, E	1,500 lb	-
NUT0062xx	A	2,000 lb	1,400 lb
	D, E	1,500 lb	-
NUT0075xx	A	2,000 lb	1,400 lb
	D, E	1,500 lb	-

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

